



eW Blast Powercore gen4, OptiField

eW Blast Powercore gen4, OptiField, 3000 K, Black housing

eW Blast Powercore gen4, OptiField, 3000 K, Black housing

eW Blast Powercore gen4, OptiField high-performance LED luminaires provide uniform lighting across large surfaces. eW Blast Powercore gen4, OptiField increases application efficiency by directing more light on a specific target and offers a range of accessories that allow for customization, along with the efficiency and cost-effectiveness of Powercore technology in a rugged die-cast aluminium housing.

Product data

General information		Light technical	
Light source color	White	Target area uniformity	3.3:1
Light source replaceable	No	Operating and electrical	
Number of gear units	1 unit	Input Voltage	100 to 277 V
Driver/power unit/transformer	Power supply unit with DMX interface	Input Frequency	50 to 60 Hz
Driver included	Yes	Power Factor (Nom)	0.9
Optical cover/lens type	Clear flat	Controls and dimming	
Protection class IEC	Safety class I	Dimmable	Yes
CE mark	CE mark	Mechanical and housing	
UL mark	UL and cUL mark	Housing Material	Aluminum die cast
Lifetime to 50% luminous flux	100000 h	Optic material	Glass
Lifetime to 70% luminous flux	84000 h	Optical cover/lens material	Tempered glass
Lifetime to 90% luminous flux	28000 h	Fixation material	Aluminum
Constant light output	Yes		
Accessory PFC	ZCP485		

eW Blast Powercore gen4, OptiField

Mounting device	Baseplate
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Color	Black

Approval and application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Vibration Standard	Complies with ANSI C136.31, 3G
Corrosion Resistance	Complies with ASTM B117 standard for > 1,500 hours
FCC mark	FCC Class B
Vibration Rating	Complies with ANSI C136.31, 3G

Initial performance (IEC compliant)

Initial luminous flux (system flux)	2521 lm
Initial LED luminaire efficacy	52.7 lm/W
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	>80
Initial input power	50 W

Over time performance (IEC compliant)

Lumen Maintenance 50% at 25°C Calculated	100000
Lumen Maintenance 50% at 25°C Reported	51000
Lumen Maintenance 50% at 50°C Calculated	100000
Lumen Maintenance 50% at 50°C Reported	51000
Lumen Maintenance 70% at 25°C Calculated	84000

Lumen Maintenance 70% at 25°C Reported	51000
Lumen Maintenance 70% at 50°C Calculated	83000
Lumen Maintenance 70% at 50°C Reported	51000
Lumen Maintenance 90% at 25°C Calculated	28000
Lumen Maintenance 90% at 25°C Reported	28000
Lumen Maintenance 90% at 50°C Calculated	27000
Lumen Maintenance 90% at 50°C Reported	28000

Application conditions


Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product data

Full product code	871829139504199
Order product name	BCP481 36xLED-HB/3000K 100-277V FTA BK
EAN/UPC - Product	8718291395041
Order code	523-000100-28
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912400135501
Net Weight (Piece)	4.146 kg
Catalog Number	523-000100-28
Catalog Number Description	eW Blast Powercore gen4, OptiField, 3000 K, Black housing



Dimensional drawing



BCP481 36xLED-HB/3000K 100-277V FTA BK

eW Blast Powercore gen4, OptiField

