



# ReachElite eW Powercore

**ReachElite High Punch Powercore, eW 300, 4000 K, 100 to 277 VAC, 2.6°, Native (no spread lens), UL/cUL, CE, CQC**

ReachElite High Punch Powercore, eW 300, 4000 K, 100 to 277 VAC, 2.6°, Native (no spread lens), UL/cUL, CE, CQC

ReachElite is a premium exterior long-throw luminaire designed to light large-scale outdoor structures ranging from bridges and facades to monuments and skyscrapers. Powerful enough to hit targets up to 970 m (3,210 ft) away with the 300 W luminaire, ReachElite raises the bar for optic quality in LED lighting. What sets ReachElite apart from the competition is its efficiency, high punch and adaptability. ReachElite delivers high-quality white light exactly where you want it, making it incredibly efficient in terms of light distribution. With a native beam angle under 3°, ReachElite introduces a new level of precision and punch to the premium exterior LED luminaire market.

## Product data

General information		Warranty period	
Lamp family code	LED-HB [ LED High Brightness]	5 years	
Light source colour	Cool white	Light technical	
Light source replaceable	No	Efficacy (lm/W) @ 2,700 K	60.3 lm/W
Driver included	Yes	Operating and electrical	
Optic type	NB [ Narrow beam]	Input Voltage	100 to 277 V
Optical cover/lens type	GT [ Tempered glass]	Input frequency	50 to 60 Hz
CE mark	CE mark		
UL mark	UL and cUL mark		

ReachElite eW Powercore

Mechanical and housing	
Housing material	Aluminum die-cast
Optic material	Glass
Optical cover/lens material	Tempered glass
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Colour	Black

Approval and application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [ 10 J]
Surge protection (common/differential)	Surge protection level until 4 kV
Vibration standard	Complies with ANSI C136.31, 3G
Vibration rating	Complies with ANSI C136.31, 3G

Initial performance (IEC compliant)	
Initial luminous flux (system flux)	17700 lm
Initial luminous flux at colour temperature of 4,000 K	17700 lm
Initial LED luminaire efficacy	60.3 lm/W
Init. Corr. Colour Temperature	4000 K
Initial input power	300 W

Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C Calculated	100000
Lumen Maintenance 50% at 25 °C Reported	72000
Lumen Maintenance 50% at 50 °C Calculated	100000
Lumen Maintenance 50% at 50 °C Reported	72000
Lumen Maintenance 70% at 25 °C Calculated	53800
Lumen Maintenance 70% at 25 °C Reported	53800


Lumen Maintenance 70% at 50 °C Calculated	53800
Lumen Maintenance 70% at 50 °C Reported	53800
Lumen Maintenance 80% at 25 °C Calculated	32700
Lumen Maintenance 80% at 25 °C Reported	28600
Lumen Maintenance 80% at 50 °C Calculated	32700
Lumen Maintenance 80% at 50 °C Reported	32700
Lumen Maintenance 90% at 25 °C Calculated	14200
Lumen Maintenance 90% at 25 °C Reported	14200
Lumen Maintenance 90% at 50 °C Calculated	14200
Lumen Maintenance 90% at 50 °C Reported	14200

Application conditions	
Ambient temperature range	-40 to +50 °C

Product data	
Full product code	871869921987100
Order product name	DCP773 108xLED-HB/4000K
EAN/UPC – product	8718699219871
Order code	523-000303-03
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	912400135526
Net Weight (Piece)	41.000 kg
Commercial Code	523-000303-03
Catalogue number description	ReachElite High Punch Powercore, eW 300, 4000 K, 100 to 277 VAC, 2.6°, Native (no spread lens), UL/cUL, CE, CQC



Dimensional drawing



DCP773 108xLED-HB/4000K

## ReachElite eW Powercore

