



ReachElite High Punch Powercore, RGBA

ReachElite High Punch Powercore, RGBA 300, RGB, 100 to 277 VAC, 2.6°, Native (no spread lens), UL/cUL, CE, CQC

ReachElite High Punch Powercore, RGBA 300, RGB, 100 to 277 VAC, 2.6°, Native (no spread lens), UL/cUL, CE, CQC

ReachElite High Punch is a premium exterior long-throw luminaire designed to light large-scale outdoor structures ranging from bridges and facades to monuments and skyscrapers. Powerful enough to hit targets up to 381 m (1,250 ft) away with the 300 W luminaire, ReachElite High Punch raises the bar for optical control, performance and beam quality in LED lighting. What sets ReachElite apart from the competition is its application efficiency, high punch, and adaptability. ReachElite delivers high-quality color light exactly where you want it. With a native beam angle under 3°, ReachElite introduces a new level of precision and punch to the premium exterior LED luminaire market.

Product data

General information		Warranty period	
Lamp family code	LED-HB [LED High Brightness]	5 years	
Light source color	RGBA	Operating and electrical	
Light source replaceable	No	Input Voltage	100 to 277 V
Driver included	Yes	Input Frequency	50 to 60 Hz
Optic type	Narrow beam	Mechanical and housing	
Optical cover/lens type	Tempered glass	Housing Material	Aluminum die cast
CE mark	CE mark	Optic material	Glass
UL mark	UL and cUL mark		

ReachElite High Punch Powercore, RGBA

Optical cover/lens material	Tempered glass
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Color	Black

Approval and application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Surge protection level until 4 kV
Vibration Standard	Complies with ANSI C136.31, 3G
Corrosion Resistance	Complies with ASTM B117 standard for > 1,500 hours
FCC mark	FCC Class A
Vibration Rating	Complies with ANSI C136.31, 3G

Initial performance (IEC compliant)

Initial luminous flux (system flux)	8853 lm
Initial LED luminaire efficacy	29.2 lm/W
Initial input power	300 W

Over time performance (IEC compliant)

Lumen Maintenance 50% at 25°C Calculated	100000
Lumen Maintenance 50% at 25°C Reported	51000
Lumen Maintenance 50% at 50°C Calculated	100000
Lumen Maintenance 50% at 50°C Reported	51000
Lumen Maintenance 70% at 25°C Calculated	49600
Lumen Maintenance 70% at 25°C Reported	49600
Lumen Maintenance 70% at 50°C Calculated	49600

Lumen Maintenance 70% at 50°C Reported	49600
Lumen Maintenance 80% at 25°C Calculated	28600
Lumen Maintenance 80% at 25°C Reported	28600
Lumen Maintenance 80% at 50°C Calculated	28600
Lumen Maintenance 80% at 50°C Reported	28600
Lumen Maintenance 90% at 25°C Calculated	10200
Lumen Maintenance 90% at 25°C Reported	10200
Lumen Maintenance 90% at 50°C Calculated	10200
Lumen Maintenance 90% at 50°C Reported	10200

Application conditions


Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product data

Full product code	871869921976500
Order product name	DCP776 108xLED-HB/RGBA
EAN/UPC - Product	8718699219765
Order code	423-000303-01
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400135528
Net Weight (Piece)	41.000 kg
Catalog Number	423-000303-01
Catalog Number Description	ReachElite High Punch Powercore, RGBA 300, RGBA, 100 to 277 VAC, 2.6°, Native (no spread lens), UL/cUL, CE, CQC



Dimensional drawing



DCP776 108xLED-HB/RGBA

ReachElite High Punch Powercore, RGBA

