



# eW Flex Compact

## eW Flex Compact, 4000 K, Narrow Beam Lens, White Housing, 12 in on-center node spacing

eW Flex Compact, 4000 K, Narrow Beam Lens, White Housing, 12 in on-center node spacing

eW Flex Compact is a versatile strand of large, individually controllable white-light LED nodes. The flexible form factor allows dynamic points of white light to be installed across almost any interior or exterior surface, including walls, ceilings, floors, and three-dimensional sculptures. eW Flex Compact can also be used to light tight alcove spaces and signage.

### Product data

General information		Controls and dimming	
Lamp family code	LED-MD [ LED Multi-die]	Dimmable	Yes
Light source replaceable	No		
Driver included	No		
Optical cover/lens type	PC-UV [ Polycarbonate bowl/cover UV-resistant]	Mechanical and housing	
CE mark	CE mark	Housing material	Polycarbonate
UL mark	UL mark	Optic material	Polycarbonate
		Colour	White
		Approval and application	
Light technical		Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Luminance per node	129758 cd/m²	Mech. impact protection code	IK10 [ 20 J vandal-resistant]
Luminous intensity (peak value) on beam axis per node	89.6 cd	FCC mark	FCC Class A
		Initial performance (IEC compliant)	
Operating and electrical		Initial luminous flux at colour temperature of 4,000 K	84 lm
Input Voltage	24 V		

eW Flex Compact

Init. Corr. Colour Temperature	4000 K
Initial input power	1 W

Over time performance (IEC compliant)

Lumen Maintenance 70% at 25 °C Calculated	56000
Lumen Maintenance 70% at 25 °C Reported	56000
Lumen Maintenance 70% at 50 °C Calculated	56000
Lumen Maintenance 70% at 50 °C Reported	56000
Lumen Maintenance 80% at 25 °C Calculated	37000
Lumen Maintenance 80% at 25 °C Reported	37000
Lumen Maintenance 80% at 50 °C Calculated	37000
Lumen Maintenance 80% at 50 °C Reported	37000
Lumen Maintenance 90% at 25 °C Calculated	20000
Lumen Maintenance 90% at 25 °C Reported	20000
Lumen Maintenance 90% at 50 °C Calculated	20000
Lumen Maintenance 90% at 50 °C Reported	20000

Application conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product data	
Full product code	871869921419799
Order product name	BGC481 50 4000K NRRW WH P305
EAN/UPC – product	8718699214197
Order code	500-000012-74
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400135801
Net Weight (Piece)	1.740 kg
Commercial Code	500-000012-74
Catalogue number description	eW Flex Compact, 4000 K, Narrow Beam Lens, White Housing, 12 in on-center node spacing

