



# iW Flex Compact

## iW Flex Compact, Clear Flat Lens, Black Housing, 4 in On-Center Node Spacing

iW Flex Compact, Clear Flat Lens, Black Housing, 4 in On-Center Node Spacing

iW Flex Compact are flexible strands of large, high-intensity, tunable-white LED nodes designed for extraordinary effects and expansive installations without the constraints of luminaire size, shape or space. Each iW Flex Compact strand consists of 50 individually addressable LED nodes, featuring dynamic integration of power, communication and control. The flexible form factor accommodates two- and three-dimensional configurations, while high light output affords superior long-distance viewing for architectural accent and perimeter lighting, large-scale signage and building-covering video displays.

### Product data

General information	
Light source colour	Cool white and warm white
Optical cover/lens type	CLFT4 [ Clear flat 4 inch separated]
Luminaire light beam spread	105°
Light technical	
Light source flux per node	80 lm
On-axis intensity in candela	31.4
CRI @ 6,500 K	83.4
CRI @ 2,700	82.1
Mechanical and housing	
Colour	White

Approval and application	
FCC mark	FCC Class A
Initial performance (IEC compliant)	
Initial input power	1 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C Calculated	100000
Lumen Maintenance 50% at 25 °C Reported	60000
Lumen Maintenance 50% at 50 °C Calculated	100000
Lumen Maintenance 50% at 50 °C Reported	60000
Lumen Maintenance 70% at 25 °C Calculated	56000
Lumen Maintenance 70% at 25 °C Reported	56000
Lumen Maintenance 70% at 50 °C Calculated	56000

iW Flex Compact

Lumen Maintenance 70% at 50 °C Reported	56000
Product data	
Full product code	871869921469299
Order product name	BGC481 50 2700-6500K CLFT BK P102
EAN/UPC – product	8718699214692
Order code	501-000016-01
SAP numerator – quantity per pack	1

Numerator – packs per outer box	6
SAP material	912400135816
Net Weight (Piece)	0.750 kg
Commercial Code	501-000016-01
Catalogue number description	iW Flex Compact, Clear Flat Lens, Black Housing, 4 in On-Center Node Spacing

