



iW Flex Compact

iW Flex Compact, Narrow Beam Lens, Black Housing, 4 in On-Center Node Spacing

iW Flex Compact, Narrow Beam Lens, Black Housing, 4 in On-Center Node Spacing

iW Flex Compact are flexible strands of large, high-intensity, tunable-white LED nodes designed for extraordinary effects and expansive installations without the constraints of luminaire size, shape or space. Each iW Flex Compact strand consists of 50 individually addressable LED nodes, featuring dynamic integration of power, communication and control. The flexible form factor accommodates two- and three-dimensional configurations, while high light output affords superior long-distance viewing for architectural accent and perimeter lighting, large-scale signage and building-covering video displays.

Product data

General information	
Light source colour	Cool white and warm white
Optical cover/lens type	PC-UV [Polycarbonate bowl/cover UV-resistant]
Luminaire light beam spread	36°
Light technical	
Light source flux per node	67 lm
On-axis intensity in candela	91.6
CRI @ 6,500 K	84.9
CRI @ 2,700	82.7

Mechanical and housing	
Colour	Black
Approval and application	
FCC mark	FCC Class A
Initial performance (IEC compliant)	
Initial input power	1 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C Calculated	100000
Lumen Maintenance 50% at 25 °C Reported	60000
Lumen Maintenance 50% at 50 °C Calculated	100000
Lumen Maintenance 50% at 50 °C Reported	60000

iW Flex Compact

Lumen Maintenance 70% at 25 °C Calculated	56000
Lumen Maintenance 70% at 25 °C Reported	56000
Lumen Maintenance 70% at 50 °C Calculated	56000
Lumen Maintenance 70% at 50 °C Reported	56000

Product data

Full product code	871869921477799
Order product name	BGC481 50 2700-6500K NRRW BK P102
EAN/UPC – product	8718699214777
Order code	501-000016-09

SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400135824
Net Weight (Piece)	0.750 kg
Commercial Code	501-000016-09
Catalogue number description	iW Flex Compact, Narrow Beam Lens, Black Housing, 4 in On-Center Node Spacing

