



eW Profile Powercore gen4

eW Profile Powercore gen4, 3000 K, 120 VAC, 997 mm (39.25 in)

eW Profile Powercore gen4, 3000 K, 120 VAC, 997 mm (39.25 in)

Profile gen4 brings advanced under-cabinet lighting to today's sophisticated kitchens. Thanks to its ultra-low profile, Profile gen4 fits seamlessly into any kitchen—from galley to grand, including retrofits and new construction. To create the right ambiance, it offers four popular color temperatures (2700 K, 3000 K, 3500 K, or 4000 K). A choice of luminaire lengths and a wide range of accessories keep installation fast and easy. Exceptional energy efficiency can generate rebates right from the start, and deliver dramatic energy savings over many years of reliable use.

Product data

| General information | | Initial input power | |
|-------------------------------------|--------------------------|--|--------|
| Optic type | Wide beam | 10 W | |
| Optical cover/lens type | Polycarbonate bowl/cover | Over time performance (IEC compliant) | |
| Luminaire light beam spread | 105° | Lumen Maintenance 50% at 25°C Calculated | 100000 |
| Mechanical and housing | | Lumen Maintenance 50% at 25°C Reported | 60000 |
| Color | White | Lumen Maintenance 50% at 50°C Calculated | 100000 |
| Approval and application | | Lumen Maintenance 50% at 50°C Reported | 60000 |
| FCC mark | FCC Class B | Lumen Maintenance 70% at 25°C Calculated | 100000 |
| Initial performance (IEC compliant) | | Lumen Maintenance 70% at 25°C Reported | 60000 |
| Init. Corr. Color Temperature | 3000 K | Lumen Maintenance 70% at 50°C Calculated | 100000 |
| | | Lumen Maintenance 70% at 50°C Reported | 60000 |
| | | Lumen Maintenance 80% at 25°C Calculated | 86000 |
| | | Lumen Maintenance 80% at 25°C Reported | 60000 |
| | | Lumen Maintenance 80% at 50°C Calculated | 65000 |

eW Profile Powercore gen4


| | |
|--|-------|
| Lumen Maintenance 80% at 50°C Reported | 60000 |
| Lumen Maintenance 90% at 25°C Calculated | 41000 |
| Lumen Maintenance 90% at 25°C Reported | 41000 |
| Lumen Maintenance 90% at 50°C Calculated | 30000 |
| Lumen Maintenance 90% at 50°C Reported | 30000 |

Product data

| | |
|--------------------|--------------------------|
| Full product code | 871869921361999 |
| Order product name | BCX413 3000 120V 997L WH |
| EAN/UPC - Product | 8718699213619 |

| | |
|---------------------------------|---|
| Order code | 523-000027-92 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 6 |
| Material Nr. (12NC) | 912400135965 |
| Net Weight (Piece) | 0.836 kg |
| Catalog Number | 523-000027-92 |
| Catalog Number Description | eW Profile Powercore gen4, 3000 K, 120 VAC, 997 mm (39.25 in) |

Dimensional drawing



BCX413 3000 120V 997L WH

