



# eW Profile Powercore gen4

**eW Profile Powercore gen4, 2700 K, 220 – 240 VAC, 489 mm (19.25 in)**

eW Profile Powercore gen4, 2700 K, 220 – 240 VAC, 489 mm (19.25 in)

Profile gen4 brings advanced under-cabinet lighting to today's sophisticated kitchens. Thanks to its ultra-low profile, Profile gen4 fits seamlessly into any kitchen – from galley to grand, including retrofits and new constructions. To create the right ambience, it offers four popular colour temperatures (2,700 K, 3,000 K, 3,500 K or 4,000 K). A choice of luminaire lengths and a wide range of accessories keep installation fast and easy. Exceptional energy-efficiency can generate rebates right from the start, and deliver dramatic energy savings over many years of reliable use.

## Product data

| General information                 |                                | Over time performance (IEC compliant)     |        |
|-------------------------------------|--------------------------------|---|--------|
| Optic type                          | WB [ Wide beam]                | Lumen Maintenance 50% at 25 °C Calculated | 100000 |
| Optical cover/lens type             | PC [ Polycarbonate bowl/cover] | Lumen Maintenance 50% at 25 °C Reported   | 60000  |
| Luminaire light beam spread         | 105°                           | Lumen Maintenance 50% at 50 °C Calculated | 100000 |
|                                     |                                | Lumen Maintenance 50% at 50 °C Reported   | 60000  |
|                                     |                                | Lumen Maintenance 70% at 25 °C Calculated | 100000 |
|                                     |                                | Lumen Maintenance 70% at 25 °C Reported   | 60000  |
|                                     |                                | Lumen Maintenance 70% at 50 °C Calculated | 100000 |
|                                     |                                | Lumen Maintenance 70% at 50 °C Reported   | 60000  |
|                                     |                                | Lumen Maintenance 80% at 25 °C Calculated | 86000  |
|                                     |                                | Lumen Maintenance 80% at 25 °C Reported   | 60000  |
|                                     |                                | Lumen Maintenance 80% at 50 °C Calculated | 65000  |
| Mechanical and housing              |                                |   |        |
| Colour                              | White                          |   |        |
| Initial performance (IEC compliant) |                                |   |        |
| Init. Corr. Colour Temperature      | 2700 K                         |   |        |
| Initial input power                 | 5.5 W                          |   |        |

eW Profile Powercore gen4


|   |       |
|---|-------|
| Lumen Maintenance 80% at 50 °C Reported   | 60000 |
| Lumen Maintenance 90% at 25 °C Calculated | 41000 |
| Lumen Maintenance 90% at 25 °C Reported   | 41000 |
| Lumen Maintenance 90% at 50 °C Calculated | 30000 |
| Lumen Maintenance 90% at 50 °C Reported   | 30000 |

Product data

|                    |                          |
|--------------------|--------------------------|
| Full product code  | 871869921369599          |
| Order product name | BCX413 2700 230V 489L WH |
| EAN/UPC – product  | 8718699213695            |

|                                   |   |
|-----------------------------------|---|
| Order code                        | 523-000102-01   |
| SAP numerator – quantity per pack | 1   |
| Numerator – packs per outer box   | 10  |
| SAP material                      | 912400135973  |
| Net Weight (Piece)                | 0.450 kg  |
| Commercial Code                   | 523-000102-01   |
| Catalogue number description      | eW Profile Powercore gen4, 2700 K, 220 – 240 VAC, 489 mm (19.25 in) |

Dimensional drawing



BCX413 2700 230V 489L WH

