



# eW Profile Powercore gen4

**eW Profile Powercore gen4, 3000 K, 220 – 240 VAC, 235 mm (9.25 in)**

eW Profile Powercore gen4, 3000 K, 220 – 240 VAC, 235 mm (9.25 in)

Profile gen4 brings advanced under-cabinet lighting to today's sophisticated kitchens. Thanks to its ultra-low profile, Profile gen4 fits seamlessly into any kitchen—from galley to grand, including retrofits and new construction. To create the right ambiance, it offers four popular color temperatures (2700 K, 3000 K, 3500 K, or 4000 K). A choice of luminaire lengths and a wide range of accessories keep installation fast and easy. Exceptional energy efficiency can generate rebates right from the start, and deliver dramatic energy savings over many years of reliable use.

## Product data

| General information                 |                          | Over time performance (IEC compliant)    |        |
|-------------------------------------|--------------------------|--|--------|
| Optic type                          | Wide beam                | Lumen Maintenance 50% at 25°C Calculated | 100000 |
| Optical cover/lens type             | Polycarbonate bowl/cover | Lumen Maintenance 50% at 25°C Reported   | 60000  |
| Luminaire light beam spread         | 105°                     | Lumen Maintenance 50% at 50°C Calculated | 100000 |
| Mechanical and housing              |                          | Lumen Maintenance 50% at 50°C Reported   | 60000  |
| Color                               | White                    | Lumen Maintenance 70% at 25°C Calculated | 100000 |
| Initial performance (IEC compliant) |                          | Lumen Maintenance 70% at 25°C Reported   | 60000  |
| Init. Corr. Color Temperature       | 3000 K                   | Lumen Maintenance 70% at 50°C Calculated | 100000 |
| Initial input power                 | 3 W                      | Lumen Maintenance 70% at 50°C Reported   | 60000  |
|                                     |                          | Lumen Maintenance 80% at 25°C Calculated | 86000  |
|                                     |                          | Lumen Maintenance 80% at 25°C Reported   | 60000  |
|                                     |                          | Lumen Maintenance 80% at 50°C Calculated | 65000  |

eW Profile Powercore gen4


|  |       |
|--|-------|
| Lumen Maintenance 80% at 50°C Reported   | 60000 |
| Lumen Maintenance 90% at 25°C Calculated | 41000 |
| Lumen Maintenance 90% at 25°C Reported   | 41000 |
| Lumen Maintenance 90% at 50°C Calculated | 30000 |
| Lumen Maintenance 90% at 50°C Reported   | 30000 |

Product data

|                    |                          |
|--------------------|--------------------------|
| Full product code  | 871869921371899          |
| Order product name | BCX413 3000 230V 235L WH |
| EAN/UPC - Product  | 8718699213718            |

|                                 |   |
|---------------------------------|---|
| Order code                      | 523-000102-03   |
| Numerator - Quantity Per Pack   | 1   |
| Numerator - Packs per outer box | 10  |
| Material Nr. (12NC)             | 912400135975  |
| Net Weight (Piece)              | 0.276 kg  |
| Catalog Number                  | 523-000102-03   |
| Catalog Number Description      | eW Profile Powercore gen4, 3000 K, 220<br>– 240 VAC, 235 mm (9.25 in) |

Dimensional drawing



BCX413 3000 230V 235L WH

