



eW Profile Powercore gen4

BCX413 3500 230V 235L WH

Wide beam - Polycarbonate bowl/cover - 105°

Profile gen4 brings advanced under-cabinet lighting to today's sophisticated kitchens. Thanks to its ultra-low profile, Profile gen4 fits seamlessly into any kitchen—from galley to grand, including retrofits and new construction. To create the right ambiance, it offers four popular color temperatures (2700 K, 3000 K, 3500 K, or 4000 K). A choice of luminaire lengths and a wide range of accessories keep installation fast and easy. Exceptional energy efficiency can generate rebates right from the start, and deliver dramatic energy savings over many years of reliable use.

Product data


General Information		Lumen Maintenance 70% at 50°C Calculated		100000
Optic type	WB [Wide beam]	Lumen Maintenance 70% at 50°C Reported	60000	
Optical cover/lens type	PC [Polycarbonate bowl/cover]	Lumen Maintenance 80% at 25°C Calculated	86000	
Luminaire light beam spread	105°	Lumen Maintenance 80% at 25°C Reported	60000	
Initial Performance (IEC Compliant)		Lumen Maintenance 80% at 50°C Calculated	65000	
Init. Corr. Color Temperature	3500 K	Lumen Maintenance 80% at 50°C Reported	60000	
Over Time Performance (IEC Compliant)		Lumen Maintenance 90% at 25°C Calculated	41000	
Lumen Maintenance 50% at 25°C Calculated	100000	Lumen Maintenance 90% at 25°C Reported	41000	
Lumen Maintenance 50% at 25°C Reported	60000	Lumen Maintenance 90% at 50°C Calculated	30000	
Lumen Maintenance 50% at 50°C Calculated	100000	Lumen Maintenance 90% at 50°C Reported	30000	
Lumen Maintenance 50% at 50°C Reported	60000	Product Data		
Lumen Maintenance 70% at 25°C Calculated	100000	Full product code	871869921374999	
Lumen Maintenance 70% at 25°C Reported	60000	Order product name	BCX413 3500 230V 235L WH	
		EAN/UPC - Product	8718699213749	

eW Profile Powercore gen4

Order code	912400135978
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Material Nr. (12NC)	912400135978
Net Weight (Piece)	0.276 kg

Dimensional drawing



eW Profile Powercore gen4

