



# ColorBlast RGB Powercore gen4

## BCP480 36xLED-HB/RGB FTA 100-277V BK

ColorBlast RGB Powercore gen4 is the next generation of indoor and outdoor floodlighting. Ideally suited for wall washing, grazing and spot lighting, ColorBlast RGB Powercore gen4 is a high-performance fixture that provides the benefits of fully saturated colors plus quality white light. It also offers a range of field-configurable beam angles, as well as the flexibility of customization with a full range of accessories that can be used in endless configurations.

### Product data

General Information	
Light source color	Red, green and blue (RGB)
CE mark	CE mark
UL mark	UL and cUL mark
Operating and Electrical	
Input Voltage	100 to 277 V
Mechanical and Housing	
Housing Material	Aluminum die-cast
Optical cover/lens material	Tempered glass
Over Time Performance (IEC Compliant)	
Lumen Maintenance 50% at 25°C Calculated	100000
Lumen Maintenance 50% at 25°C Reported	72000
Lumen Maintenance 50% at 50°C Calculated	100000
Lumen Maintenance 50% at 50°C Reported	72000
Lumen Maintenance 70% at 25°C Calculated	100000
Lumen Maintenance 70% at 25°C Reported	72000

Lumen Maintenance 70% at 50°C Calculated	100000
Lumen Maintenance 70% at 50°C Reported	72000
Lumen Maintenance 80% at 25°C Calculated	100000
Lumen Maintenance 80% at 25°C Reported	72000
Lumen Maintenance 80% at 50°C Calculated	100000
Lumen Maintenance 80% at 50°C Reported	72000
Lumen Maintenance 90% at 25°C Calculated	51400
Lumen Maintenance 90% at 25°C Reported	51400
Lumen Maintenance 90% at 50°C Calculated	51400
Lumen Maintenance 90% at 50°C Reported	51400


### Product Data

Order product name	BCP480 36xLED-HB/RGB FTA 100-277V BK
EAN/UPC - Product	8718699217402
Order code	912400136057
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912400136057

# ColorBlast RGB Powercore gen4

Net Weight (Piece) 4.146 kg

## Dimensional drawing



ColorBlast FTA

