



ColorBlast IntelliHue Powercore gen4, OptiField



ColorBlast IntelliHue Powercore gen4, OptiField, 100 to 277 VAC, White Housing

ColorBlast IntelliHue Powercore gen4, OptiField, 100 to 277 VAC,
White Housing

ColorBlast IntelliHue Powercore gen4 produces high-quality white, pastel, and saturated color light, in the same precisely controllable luminaire. IntelliHue technology delivers exceptional CRI and the ability to choose any CCT between 2000 K and 10000 K. OptiField technology delivers extremely uniform illuminance, providing smooth, even light and subtle shading with reduced setbacks—without hotspots or banding. ColorBlast IntelliHue Powercore offers a range of accessories that allow for customizable beam angles for floodlighting, spotlighting, wall washing, and grazing, along with the efficiency and cost-effectiveness of Powercore technology in a rugged die-cast aluminium housing.

Product data

General information		Light technical	
Light source color	IntelliHue	Target area uniformity	4.2:1
Driver/power unit/transformer	-	Efficacy (lm/W) @ 4000 K	46.7 lm/W
Driver included	Yes	Efficacy (lm/W) @ 2700 K	51.9 lm/W
CE mark	CE mark	CRI @ 4000 K	91
UL mark	UL and cUL mark	CRI @ 2700	92


ColorBlast IntelliHue Powercore gen4, OptiField

Operating and electrical	
Input Voltage	100 to 277 V
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Housing Material	Aluminum die cast
Optical cover/lens material	Tempered glass
Color	White
Approval and application	
Energy Efficiency Class	G
Vibration Standard	Complies with ANSI C136.31, 3G
Corrosion Resistance	Complies with ASTM B117 standard for > 1,500 hours
FCC mark	FCC Class A
Vibration Rating	Complies with ANSI C136.31, 3G
EPREL Registration Number	887783
Initial performance (IEC compliant)	
Initial input power	50 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25°C Calculated	90300
Lumen Maintenance 50% at 25°C Reported	54000
Lumen Maintenance 50% at 50°C Calculated	90300
Lumen Maintenance 50% at 50°C Reported	54000
Lumen Maintenance 70% at 25°C Calculated	46100
Lumen Maintenance 70% at 25°C Reported	46100

Lumen Maintenance 70% at 50°C Calculated	46100
Lumen Maintenance 70% at 50°C Reported	46100
Lumen Maintenance 80% at 25°C Calculated	28600
Lumen Maintenance 80% at 25°C Reported	28600
Lumen Maintenance 80% at 50°C Calculated	28600
Lumen Maintenance 80% at 50°C Reported	28600
Lumen Maintenance 90% at 25°C Calculated	13100
Lumen Maintenance 90% at 25°C Reported	13100
Lumen Maintenance 90% at 50°C Calculated	13100
Lumen Maintenance 90% at 50°C Reported	13100

Application conditions	
Ambient temperature range	-40 to +50 °C
Product data	
Full product code	871869921742699
Order product name	BCP483 36xLED-HB/RGBM FTA 100-277V WH
EAN/UPC - Product	8718699217426
Order code	423-000017-00
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	912400136059
Net Weight (Piece)	4.146 kg
Catalog Number	423-000017-00
Catalog Number Description	ColorBlast IntelliHue Powercore gen4, OptiField, 100 to 277 VAC, White Housing

Dimensional drawing



BCP483 36xLED-HB/RGBM FTA 100-277V WH

ColorBlast IntelliHue Powercore gen4, OptiField

