



# Vaya Linear LP G2

BCP422 G2 120 4000 L1200 CE CQC PSE

LED High Brightness

Vaya Linear LP is a super slim outdoor linear luminaire for low-level grazing applications, with wide 120° beam or elliptical 28° x 84° optics. Its slim form factor is ideal for space-restricted applications with limited setback or allowable install height. The robust Vaya Linear LP G2 offers a variety of color and white CCT options with either static on/off- or dynamic control options via standard DMX-512. The discreet design with integrated power supply and waterproof connectors makes wiring simple, fast and reliable.

## Product data

General Information	
Lamp family code	LED-HB [ LED High Brightness]
Light source color	Neutral white
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	GT [ Tempered glass]
Luminaire light beam spread	120°
CE mark	CE mark
UL mark	-
CQC mark	CQC-mark
PSE mark	PSE mark
FCC mark	-
Operating and Electrical	
Input Voltage	100 to 240 V
Input Frequency	50 to 60 Hz
Mechanical and Housing	
Housing Material	Aluminum extruded

Optic material	Glass
Optical cover/lens material	Tempered glass
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [ 2 J reinforced]
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	1498 lm
Initial luminous flux at color temperature of 4000 K	1498 lm
Initial LED luminaire efficacy	86.6 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	83
Initial input power	17.2 W
Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	100000

Vaya Linear LP G2

Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	100000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	87000
Lumen Maintenance 80% at 25°C Reported	60000
Lumen Maintenance 80% at 40°C Calculated	66000
Lumen Maintenance 80% at 40°C Reported	60000
Lumen Maintenance 90% at 25°C Calculated	41000
Lumen Maintenance 90% at 25°C Reported	41000
Lumen Maintenance 90% at 40°C Calculated	31000
Lumen Maintenance 90% at 40°C Reported	31000


Application Conditions

Ambient temperature range	-40 to +104 °F
---------------------------	----------------

Product Data	
Full product code	871869921812699
Order product name	BCP422 G2 120 4000 L1200 CE CQC PSE
EAN/UPC - Product	8718699218126
Order code	912400136124
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400136124
Net Weight (Piece)	1.860 kg



Dimensional drawing



Vaya Linear LP Gen2

