



# Vaya Linear LP G2, White

Vaya Linear LP G2, 4000 K, 120°, 1.2 m (4 ft), CE/CQC/PSE

Vaya Linear LP G2, 4000 K, 120°, 1.2 m (4 ft), CE/CQC/PSE

Vaya Linear LP is a super slim outdoor linear luminaire for low-level grazing applications, with wide 120° beam or elliptical 28° x 84° optics. Its slim form factor is ideal for space-restricted applications with limited setback or allowable install height. The robust Vaya Linear LP G2 offers a variety of color and white CCT options with static on/off control. Dynamic control options via standard DMX-512 are available by custom order. The discreet design with integrated power supply and waterproof connectors makes wiring simple, fast and reliable.

## Product data

General information		Input Frequency	
Lamp family code	LED-HB [ LED High Brightness]	50 to 60 Hz	
Light source color	Neutral white	Mechanical and housing	
Light source replaceable	No	Housing Material	Aluminum extruded
Driver included	Yes	Optic material	Glass
Optical cover/lens type	Tempered glass	Optical cover/lens material	Tempered glass
Luminaire light beam spread	120°	Optical cover/lens shape	Flat
CE mark	CE mark	Optical cover/lens finish	Clear
UL mark	-	Color	Dark gray
CQC mark	CQC-mark	Approval and application	
PSE mark	PSE mark	Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Operating and electrical		Mech. impact protection code	IK07 [ 2 J reinforced]
Input Voltage	100 to 240 V		

Vaya Linear LP G2, White

Vibration Standard	Complies with ANSI C136.31
FCC mark	-
Vibration Rating	Complies with ANSI C136.31

Initial performance (IEC compliant)

Initial luminous flux (system flux)	1498 lm
Initial luminous flux at color temperature of 4000 K	1498 lm
Initial LED luminaire efficacy	86.6 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	83
Initial input power	17.2 W

Over time performance (IEC compliant)

Lumen Maintenance 70% at 25°C Calculated	100000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	100000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	87000
Lumen Maintenance 80% at 25°C Reported	60000
Lumen Maintenance 80% at 40°C Calculated	66000
Lumen Maintenance 80% at 40°C Reported	60000
Lumen Maintenance 90% at 25°C Calculated	41000

Lumen Maintenance 90% at 25°C Reported	41000
Lumen Maintenance 90% at 40°C Calculated	31000
Lumen Maintenance 90% at 40°C Reported	31000

Application conditions

Ambient temperature range	-40 to +40 °C
---------------------------	---------------

Product data

Full product code	871869921812699
Order product name	BCP422 G2 120 4000 L1200 CE CQC PSE
EAN/UPC - Product	8718699218126
Order code	350-000018-06
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400136124
Net Weight (Piece)	1.860 kg
Catalog Number	350-000018-06
Catalog Number Description	Vaya Linear LP G2, 4000 K, 120°, 1.2 m (4 ft), CE/CQC/PSE

