



# Vaya Linear LP G2

BCP422 G2 28x84 4000 L1200 CE CQC PSE

## LED High Brightness

Vaya Linear LP is a super slim outdoor linear luminaire for low-level grazing applications, with wide 120° beam or elliptical 28° x 84° optics. Its slim form factor is ideal for space-restricted applications with limited setback or allowable install height. The robust Vaya Linear LP G2 offers a variety of color and white CCT options with either static on/off- or dynamic control options via standard DMX-512. The discreet design with integrated power supply and waterproof connectors makes wiring simple, fast and reliable.

## Product data

General Information	
Lamp family code	LED-HB [ LED High Brightness]
Light source color	Neutral white
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	GT [ Tempered glass]
CE mark	CE mark
UL mark	-
CQC mark	CQC-mark
PSE mark	PSE mark
Operating and Electrical	
Input Voltage	100 to 240 V
Input Frequency	50 to 60 Hz
Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Glass

Optical cover/lens material	Tempered glass
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Color	Dark gray
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [ 2 J reinforced]
Vibration Standard	Complies with ANSI C136.31
Vibration Rating	Complies with ANSI C136.31
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	1774 lm
Initial luminous flux at color temperature of 4000 K	1774 lm
Initial LED luminaire efficacy	102.7 lm/W
Init. Corr. Color Temperature	4000 K

Vaya Linear LP G2


Init. Color Rendering Index	83
Initial input power	17.2 W

Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	100000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	100000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Calculated	87000
Lumen Maintenance 80% at 25°C Reported	60000
Lumen Maintenance 80% at 40°C Calculated	66000
Lumen Maintenance 80% at 40°C Reported	60000
Lumen Maintenance 90% at 25°C Calculated	41000
Lumen Maintenance 90% at 25°C Reported	41000
Lumen Maintenance 90% at 40°C Calculated	31000
Lumen Maintenance 90% at 40°C Reported	31000

Application Conditions	
Ambient temperature range	-40 to +40 °C
Product Data	
Full product code	871869921813399
Order product name	BCP422 G2 28x84 4000 L1200 CE
	CQC PSE
EAN/UPC - Product	8718699218133
Order code	912400136125
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400136125
Net Weight (Piece)	2.150 kg



Dimensional drawing



Vaya Linear LP Gen2

