



iColor Accent Compact, RGBW

iColor Accent Compact, RGBW, 315 mm (12.4 in), Clear Lens

iColor Accent Compact, RGBW, 315 mm (12.4 in), Clear Lens

iColor Accent Compact, RGBW is a direct view linear LED luminaire ideally suited for displaying large-scale video, graphics and intricately designed effects in a host of architectural settings. iColor Accent Compact, RGBW adds a separate white LED, creating better-quality whites compared to RGB. iColor Accent Compact, RGBW accepts Ethernet input from the PDS-400 48V EO to support long control runs not subject to DMX data and addressing limitations. Two lens choices are available for iColor Accent Compact, RGBW: a clear lens which delivers the brightest output and a translucent lens which provides the widest viewing angle.

Product data

General information	
Light source colour	RGBW
Optical cover/lens type	PC-UV [Polycarbonate bowl/cover UV-resistant]
Luminaire light beam spread	105°
Light technical	
On-axis intensity in candela	101
Mechanical and housing	
Length	305 mm
Colour	Aluminum

Approval and application	
Energy Efficiency Class	G
Vibration standard	Complies with ANSI C136.31, 3G
FCC mark	FCC Class A
Vibration rating	Complies with ANSI C136.31, 3G
	942290
Initial performance (IEC compliant)	
Initial LED luminaire efficacy at RGB operation	28.7 lm/W
Initial input power	10 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C Reported	60000

iColor Accent Compact, RGBW


Lumen Maintenance 50% at 50 °C Reported	60000
Lumen Maintenance 70% at 25 °C Reported	60000
Lumen Maintenance 70% at 50 °C Reported	60000
Lumen Maintenance 80% at 25 °C Reported	60000
Lumen Maintenance 80% at 50 °C Reported	60000

Product data

Full product code	871869921874499
Order product name	BCS425 RGBW CL ETH L305 PP19
EAN/UPC – product	8718699218744

Order code	101-000200-10
SAP numerator – quantity per pack	1
Numerator – packs per outer box	9
SAP material	912400136259
Net Weight (Piece)	0.610 kg
Commercial Code	101-000200-10
Catalogue number description	iColor Accent Compact, RGBW, 315 mm (12.4 in), Clear Lens

Dimensional drawing



BCS425 RGBW CL ETH L305 PP19



BCS425 RGBW CL ETH L305 PP19

