



# Accent Compact, RGBW



## iColor Accent Compact, RGBW, 619.5 mm (24.4 in), Clear Lens

iColor Accent Compact, RGBW, 619.5 mm (24.4 in), Clear Lens

iColor Accent Compact, RGBW is a direct view linear LED luminaire ideally suited for displaying large-scale video, graphics, and intricately designed effects in a host of architectural settings. iColor Accent Compact, RGBW adds a separate white LED, creating better-quality whites compared to RGB. iColor Accent Compact, RGBW accepts Ethernet input from the PDS-400 48V EO to support long control runs not subject to DMX data and addressing limitations. Two lens choices are available for iColor Accent Compact, RGBW: a clear lens which delivers the brightest output and a translucent lens which provides the widest viewing angle.

### Product data

| General information          |                                       |
|------------------------------|---------------------------------------|
| Light source color           | RGBW                                  |
| Optical cover/lens type      | Polycarbonate bowl/cover UV-resistant |
| Luminaire light beam spread  | 105°                                  |
| Light technical              |                                       |
| On-axis intensity in candela | 101                                   |
| Mechanical and housing       |                                       |
| Length                       | 610 mm                                |
| Color                        | Aluminum                              |


| Approval and application                        |  |
|---|--|
| Energy Efficiency Class                         | G  |
| Vibration Standard                              | Complies with ANSI C136.31, 3G                     |
| Corrosion Resistance                            | Complies with ASTM B117 standard for > 1,500 hours |
| FCC mark  | FCC Class A  |
| Vibration Rating                                | Complies with ANSI C136.31, 3G                     |
| EPREL Registration Number                       | 942292   |
| Initial performance (IEC compliant)             |  |
| Initial LED luminaire efficacy at RGB operation | 35.8 lm/W  |

Accent Compact, RGBW


|  |                 |
|--|-----------------|
| Initial input power                    | 16 W            |
| Over time performance (IEC compliant)  |                 |
| Lumen Maintenance 50% at 25°C Reported | 60000           |
| Lumen Maintenance 50% at 50°C Reported | 60000           |
| Lumen Maintenance 70% at 25°C Reported | 60000           |
| Lumen Maintenance 70% at 50°C Reported | 60000           |
| Lumen Maintenance 80% at 25°C Reported | 50000           |
| Lumen Maintenance 80% at 50°C Reported | 50000           |
| Product data                           |                 |
| Full product code                      | 871869921876899 |

|                                 |   |
|---------------------------------|---|
| Order product name              | BCS425 RGBW CL ETH L610 PP19                                |
| EAN/UPC - Product               | 8718699218768   |
| Order code                      | 101-000200-12   |
| Numerator - Quantity Per Pack   | 1   |
| Numerator - Packs per outer box | 9   |
| Material Nr. (12NC)             | 912400136261  |
| Net Weight (Piece)              | 0.960 kg  |
| Catalog Number                  | 101-000200-12   |
| Catalog Number Description      | iColor Accent Compact, RGBW, 619.5 mm (24.4 in), Clear Lens |

Dimensional drawing



BCS425 RGBW CL ETH L610 PP19



BCS425 RGBW CL ETH L610 PP19

