



SofTrace Recessed Fluorescent

2x2, 2 Lamp CF40, Diffuse (Ribbed) Center Diffuser

2x2, 2 Lamp CF40, Diffuse (Ribbed) Center Diffuser

SofTrace brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information	
Lamp Envelope Code	TT5
Lamp Source Code	Fluorescent
Lamp Watts	40
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	70
Mechanical and Housing	
Fixture Size	2 ft x 2 ft

Product Data	
Order product name	2STG2CF40-D-UNV
EAN/UPC - Product	734340000795
Order code	2STG2CF40-D-UNV-1/2-EB
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400342166
Net Weight (Piece)	0.001 kg
Catalog Number	2STG2CF40-D-UNV-1/2-EB
Catalog Number Description	2x2, 2 Lamp CF40, Diffuse (Ribbed) Center Diffuser