



# 60 Series Exits

## ER60MLD3GGA

Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Green Letters, Gray Housing and Brushed Aluminum Stencil, Emergency Ni-Cad Battery, Self Diagnostics

The 60 Line Max is designed to meet the demands of todays most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

### Product data

<b>General Information</b>		<b>Local order code</b>	4005460
Lamp Source Code	LED	Numerator - Quantity Per Pack	1
Mounting	Wall Suspended	Numerator - Packs per outer box	1
<b>Operating and Electrical</b>		Material Nr. (12NC)	912400342485
Voltages	120/277 V	Net Weight (Piece)	0.100 kg
Luminaire Input Watts	4	Commercial Code	ER60MLD3GGA
<b>Product Data</b>		Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Green Letters, Gray Housing and Brushed Aluminum Stencil, Emergency Ni-Cad Battery, Self Diagnostics
Order product name	ER60MLD3GGA	Quick Ship	-
EAN/UPC - Product	734340054606		
Order code	912400342485		