



LP3 Recessed Paralouver

2x2, 2 Lamp 31U6T8, 9 Cell, Semi-Specular Low Iridescence Anodized Aluminum Louver

2x2, 2 Lamp 31U6T8, 9 Cell, Semi-Specular Low Iridescence Anodized Aluminum Louver

The LP3 Paralouver Recessed is designed to provide the optimum balance of visual comfort, luminaire efficiency and low cost.

Product data

| General Information | |
|-------------------------------|---------------|
| Lamp Envelope Code | T-8 Bent |
| Lamp Source Code | Fluorescent |
| Lamp Watts | 31 |
| Number of Lamps | 2 |
| Photometric Distribution Type | Direct |
| Mounting | Recessed |
| Operating and Electrical | |
| Voltages | 120/277/347 V |
| Mechanical and Housing | |
| Fixture Size | 2 ft x 2 ft |

| Product Data | |
|---------------------------------|--|
| Order product name | 2LP3GS231U6R-33AL-UNV |
| EAN/UPC - Product | 734340079876 |
| Order code | 2LP3GS231U6R-33AL-UNV-1/2-EB |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912400342634 |
| Net Weight (Piece) | 0.001 kg |
| Catalog Number | 2LP3GS231U6R-33AL-UNV-1/2-EB |
| Catalog Number Description | 2x2, 2 Lamp 31U6T8, 9 Cell, Semi-Specular Low Iridescence Anodized Aluminum Louver |