



# Industrial Docklight

## 42" Adjustable Arm, 150w MAX. PAR 38 or R40 Lamp

42" Adjustable Arm, 150w MAX. PAR 38 or R40 Lamp

Rugged flexibility combined with incredible energy savings is probably the best way to describe this beautifully designed Dock Light. Incorporating a robust die cast exterior, this dock light is designed to withstand the rigorous demands of shipping and receiving areas.

### Product data

<b>General Information</b>		<b>EAN/UPC - Product</b>	734340081749
Lamp Source Code	Incandescent	<b>Order code</b>	ID1K42-120
Lamp Watts	150	<b>Numerator - Quantity Per Pack</b>	1
Number of Lamps	1	<b>Numerator - Packs per outer box</b>	1
Mounting	Surface Wall	<b>Material Nr. (12NC)</b>	912400342644
<b>Operating and Electrical</b>		<b>Net Weight (Piece)</b>	0.001 kg
Voltages	120 V	<b>Catalog Number</b>	ID1K42-120
<b>Product Data</b>		<b>Catalog Number Description</b>	42" Adjustable Arm, 150w MAX. PAR 38 or R40 Lamp
Order product name	ID1K42-120		