



# SofTrace Recessed Fluorescent

## 2STG232-PMW-UNV

2x4, 2 Lamp F32T8, Round Perforated w/White Overlay Center Diffuser

SofTrace brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

### Product data

General Information		Product Data	
Lamp Envelope Code	T-8	Order product name	2STG232-PMW-UNV
Lamp Source Code	Fluorescent	EAN/UPC - Product	734340239836
Lamp Watts	32	Order code	912400343499
Number of Lamps	2	Local order code	4023983
Photometric Distribution Type	Direct	Numerator - Quantity Per Pack	1
Mounting	Recessed	Numerator - Packs per outer box	1
<b>Operating and Electrical</b>		Material Nr. (12NC)	912400343499
Voltages	120/277/347 V	Net Weight (Piece)	0.001 kg
Luminaire Input Watts	61	Commercial Code	2STG232-PMW-UNV-1/2-EB10R
<b>Mechanical and Housing</b>		Catalog Number Description	2x4, 2 Lamp F32T8, Round Perforated w/White Overlay Center Diffuser
Fixture Size	2 ft x 4 ft	Quick Ship	-