



# SofTrace Recessed Fluorescent

## 2x4, 2 Lamp F32T8, Round Perforated w/White Overlay Center Diffuser

2x4, 2 Lamp F32T8, Round Perforated w/White Overlay Center Diffuser

SofTrace brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

### Product data

General Information		Mechanical and Housing	
Lamp Envelope Code	T-8	Fixture Size	2 ft x 4 ft
Lamp Source Code	Fluorescent	Product Data	
Lamp Watts	32	Order product name	2STG232-PMW-UNV
Number of Lamps	2	EAN/UPC - Product	734340239836
Photometric Distribution Type	Direct	Order code	2STG232-PMW-UNV-1/2-EB10R
Mounting	Recessed	Numerator - Quantity Per Pack	1
Operating and Electrical		Numerator - Packs per outer box	1
Voltages	120/277/347 V	Material Nr. (12NC)	912400343499
Luminaire Input Watts	61	Net Weight (Piece)	0.001 kg
		Catalog Number	2STG232-PMW-UNV-1/2-EB10R

SofTrace Recessed Fluorescent

Catalog Number	Description
	2x4, 2 Lamp F32T8, Round Perforated w/White Overlay Center Diffuser

