



60 Series Exits

ER60MLD3RG

Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Red Letters, Gray Housing and Gray Stencil, Emergency Ni-Cad Battery, Self Diagnostics

The 60 Line Max is designed to meet the demands of today's most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

Product data

General Information	
Lamp Source Code	LED
Mounting	Wall Suspended
Operating and Electrical	
Voltages	120/277 V
Luminaire Input Watts	4
Product Data	
Order product name	ER60MLD3RG
EAN/UPC - Product	734340378900
Order code	912400344202

Local order code	-
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400344202
Net Weight (Piece)	0.100 kg
Commercial Code	ER60MLD3RG
Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Red Letters, Gray Housing and Gray Stencil, Emergency Ni-Cad Battery, Self Diagnostics
Quick Ship	-