



# 1F Specification Industrial

## 4', 3 Lamp F32T8, Painted Polyester Reflector, 10% Uplight

4', 3 Lamp F32T8, Painted Polyester Reflector, 10% Uplight

The 1F Specification Industrial is a heavy duty industrial fluorescent luminaire providing 10 % uplight and 13° crosswise shielding.

### Product data

General Information	
Lamp Envelope Code	T-8
Lamp Source Code	Fluorescent
Lamp Watts	32
Number of Lamps	3
Photometric Distribution Type	Direct
Mounting	Surface Suspended
Operating and Electrical	
Voltages	120/277/347 V
Mechanical and Housing	
Fixture Size	48 in
Shape	Linear

Product Data	
Order product name	1F332-PP-UNV
EAN/UPC – product	734340935455
Order code	1F332-PP-UNV-1/3-EB
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	912400347058
Net weight (piece)	0.001 kg
Commercial Code	1F332-PP-UNV-1/3-EB
Commercial Code	4', 3 Lamp F32T8, Painted Polyester Reflector, 10% Uplight