



# SofTrace Recessed Fluorescent

## 2STG232-DS-UNV

2x4, 2 Lamp F32T8, Diffuse (Smooth) Center Diffuser

SofTrace brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

### Product data

General Information	
Lamp Envelope Code	T-8
Lamp Source Code	Fluorescent
Lamp Watts	32
Number of Lamps	2
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	59
Mechanical and Housing	
Fixture Size	2 ft x 4 ft

Product Data	
Order product name	2STG232-DS-UNV
EAN/UPC - Product	782343202685
Order code	912400348341
Local order code	4320268
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400348341
Net Weight (Piece)	0.001 kg
Commercial Code	2STG232-DS-UNV-1/2-EB
Catalog Number Description	2x4, 2 Lamp F32T8, Diffuse (Smooth) Center Diffuser
Quick Ship	-