



# 1F Specification Industrial

## 1F232-PP-UNV

4', 2 Lamp F32T8, Painted Polyester Reflector, 10% Uplight

The 1F Specification Industrial is a heavy duty industrial fluorescent luminaire providing 10% uplight and 13° crosswise sheilding.

### Product data

| General Information           |                   |
|-------------------------------|-------------------|
| Lamp Envelope Code            | T-8               |
| Lamp Source Code              | Fluorescent       |
| Lamp Watts                    | 32                |
| Number of Lamps               | 2                 |
| Photometric Distribution Type | Semi Direct       |
| Mounting                      | Surface Suspended |
| Operating and Electrical      |                   |
| Voltages                      | 120/277/347 V     |
| Mechanical and Housing        |                   |
| Fixture Size                  | 48 in             |
| Shape                         | Linear            |

| Product Data                    |  |
|---------------------------------|--|
| Order product name              | 1F232-PP-UNV   |
| EAN/UPC - Product               | 782343241295   |
| Order code                      | 912400348691   |
| Local order code                | 4324129  |
| Numerator - Quantity Per Pack   | 1  |
| Numerator - Packs per outer box | 1  |
| Material Nr. (12NC)             | 912400348691   |
| Net Weight (Piece)              | 0.001 kg   |
| Commercial Code                 | 1F232-PP-UNV-1/2-EB  |
| Catalog Number Description      | 4', 2 Lamp F32T8, Painted Polyester Reflector, 10% Uplight |
| Quick Ship                      | -  |