



# 1F Specification Industrial

## 4', 2 Lamp F32T8, Painted Polyester Reflector, 10% Uplight

4', 2 Lamp F32T8, Painted Polyester Reflector, 10% Uplight

The 1F Specification Industrial is a heavy duty industrial fluorescent luminaire providing 10% uplight and 13° crosswise sheilding.

### Product data

General Information	
Lamp Envelope Code	T-8
Lamp Source Code	Fluorescent
Lamp Watts	32
Number of Lamps	2
Photometric Distribution Type	Semi Direct
Mounting	Surface Suspended
Operating and Electrical	
Voltages	120/277/347 V
Mechanical and Housing	
Shape	Linear

Product Data	
Order product name	1F232-PP-UNV
EAN/UPC - Product	782343241295
Order code	1F232-PP-UNV-1/2-EB
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400348691
Net Weight (Piece)	0.001 kg
Catalog Number	1F232-PP-UNV-1/2-EB
Catalog Number Description	4', 2 Lamp F32T8, Painted Polyester Reflector, 10% Uplight