



SofTrace Recessed Fluorescent

2x2, 2 Lamp CF40, Diffuse (Smooth) Center Diffuser

2x2, 2 Lamp CF40, Diffuse (Smooth) Center Diffuser

SofTrace brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

Product data

General Information		Product Data	
Lamp Envelope Code	TT5	Order product name	2STG2CF40-DS-UNV
Lamp Source Code	Fluorescent	EAN/UPC - Product	782343340288
Lamp Watts	40	Order code	2STG2CF40-DS-UNV-1/2-EB
Number of Lamps	2	Numerator - Quantity Per Pack	1
Photometric Distribution Type	Direct	Numerator - Packs per outer box	1
Mounting	Recessed	Material Nr. (12NC)	912400349277
Operating and Electrical		Net Weight (Piece)	0.001 kg
Voltages	120/277/347 V	Catalog Number	2STG2CF40-DS-UNV-1/2-EB
Luminaire Input Watts	70	Catalog Number Description	2x2, 2 Lamp CF40, Diffuse (Smooth) Center Diffuser
Mechanical and Housing			
Fixture Size	2 ft x 2 ft		