



# 60 Series Exits

## ER60MLD3GWA

Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Green Letters, White Housing and Brushed Aluminum Stencil, Emergency Ni-Cad Battery, Self Diagnostics

The 60 Line Max is designed to meet the demands of todays most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

### Product data

General Information	
Lamp Source Code	LED
Mounting	Wall Suspended
Operating and Electrical	
Voltages	120/277 V
Luminaire Input Watts	4
Product Data	
Order product name	ER60MLD3GWA
EAN/UPC - Product	782343411377
Order code	912400349870

Local order code	-
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400349870
Net Weight (Piece)	0.100 kg
Commercial Code	ER60MLD3GWA
Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Green Letters, White Housing and Brushed Aluminum Stencil, Emergency Ni-Cad Battery, Self Diagnostics
Quick Ship	-