



DuaLED Recessed

2x4, 4300 Nominal Delivered Lumens, 3500K, Diffuse

2x4, 4300 Nominal Delivered Lumens, 3500K, Diffuse - 105 lm/W

DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	41

Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular

Initial Performance (IEC Compliant)	
Luminaire Lumens	4300
Efficacy	105 lm/W

Product Data	
Order product name	2DLG43L835-4-D-UNV
EAN/UPC - Product	782343815458
Order code	2DLG43L835-4-D-UNV-DIM

DuaLED Recessed

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400359283
Net Weight (Piece)	9.000 kg

Catalog Number	2DLG43L835-4-D-UNV-DIM
Catalog Number Description	2x4, 4300 Nominal Delivered Lumens, 3500K, Diffuse

