



# DuaLED Recessed

## 2DLG73L835-4-D-UNV

2x4, 7300 Nominal Delivered Lumens, 3500K, Diffuse - 99 lm/W

DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare.

### Product data

General Information	
Lamp Source Code	LED
Color Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	74
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular

Initial Performance (IEC Compliant)	
Luminaire Lumens	7300
Efficacy	99 lm/W
Product Data	
Order product name	2DLG73L835-4-D-UNV
EAN/UPC - Product	782343820230
Order code	912400359615
Local order code	4382023
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400359615
Net Weight (Piece)	0.001 kg
Commercial Code	2DLG73L835-4-D-UNV-DIM
Catalog Number Description	2x4, 7300 Nominal Delivered Lumens, 3500K, Diffuse
Quick Ship	Spec Smart (10 Days) USA

