



DuaLED Surface LED

1SDL27L840-4-D-UNV

1x4, 2700 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse - 96 lm/W

Surface DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare. Optional SpaceWise automated wireless technology provides integrated occupancy and daylight harvesting for additional control and energy savings with no reduction of life.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Surface
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	28

Mechanical and Housing	
Fixture Size	1 ft x 4 ft
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	2700
Efficacy	96 lm/W
Product Data	
Order product name	1SDL27L840-4-D-UNV
EAN/UPC - Product	782343866924
Order code	912400363134

DuaLED Surface LED

Local order code	4386692
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400363134
Net Weight (Piece)	0.100 kg
Commercial Code	1SDL27L840-4-D-UNV-DIM

Catalog Number Description	1x4, 2700 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse
Quick Ship	-

