



DuaLED Recessed

2x2, 3800 Nominal Delivered Lumens, 3500K, Diffuse

2x2, 3800 Nominal Delivered Lumens, 3500K, Diffuse - 97 lm/W

DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare.

Product data

General Information		Shape	
Lamp Source Code	LED	Square	
Colour Temperature	3500K	Initial Performance (IEC Compliant)	
CRI	80	Luminaire Lumens	3800
Photometric Distribution Type	Direct	Efficacy	97 lm/W
Mounting	Recessed	Product Data	
Operating and Electrical		Order product name	2DLG38L835-2-D-UNV
Voltages	120/277/347 V	EAN/UPC - Product	782343882276
Luminaire Input Watts	39	Order code	2DLG38L835-2-D-UNV-DIM
Mechanical and Housing		Numerator - Quantity Per Pack	1
Fixture Size	2 ft x 2 ft	Numerator - Packs per outer box	1
		Material Nr. (12NC)	912400364135

DuaLED Recessed

Net Weight (Piece)	0.001 kg
Catalog Number	2DLG38L835-2-D-UNV-DIM
Catalog Number Description	2x2, 3800 Nominal Delivered Lumens, 3500K, Diffuse

