



# SP Static Recessed Lensed

## 2x4, 4 Lamp F32T8, Prismatic Acrylic Lens

2x4, 4 Lamp F32T8, Prismatic Acrylic Lens

The SP Static Lensed Troffer is a specification grade recessed lensed luminaire and offers many premium options.

### Product data

General Information		Product Data	
Lamp Envelope Code	T-8	Order product name	2SPG432-FS12-UNV
Lamp Source Code	Fluorescent	EAN/UPC - Product	781370713430
Lamp Watts	32	Order code	2SPG432-FS12-UNV-1/4-EB10R
Number of Lamps	4	Numerator - Quantity Per Pack	1
Mounting	Recessed	Numerator - Packs per outer box	1
Operating and Electrical		Material Nr. (12NC)	912400371630
Voltages	120/277/347 V	Net Weight (Piece)	10.300 kg
Mechanical and Housing		Catalog Number	2SPG432-FS12-UNV-1/4-EB10R
Fixture Size	2 ft x 4 ft	Catalog Number Description	2x4, 4 Lamp F32T8, Prismatic Acrylic Lens