



SP Static Recessed Lensed

2x2, 3 Lamp F17T8, Prismatic Acrylic Lens

2x2, 3 Lamp F17T8, Prismatic Acrylic Lens

The SP Static Lensed Troffer is a specification grade recessed lensed luminaire and offers many premium options.

Product data

General Information		Product Data	
Lamp Envelope Code	T-8	Order product name	2SPG317R-FS12-UNV
Lamp Source Code	Fluorescent	EAN/UPC - Product	781370793807
Lamp Watts	17	Order code	2SPG317R-FS12-UNV-1/3-EB
Number of Lamps	3	Numerator - Quantity Per Pack	1
Mounting	Recessed	Numerator - Packs per outer box	1
Operating and Electrical		Material Nr. (12NC)	912400372137
Voltages	120/277/347 V	Net Weight (Piece)	0.001 kg
Mechanical and Housing		Catalog Number	2SPG317R-FS12-UNV-1/3-EB
Fixture Size	2 ft x 2 ft	Catalog Number Description	2x2, 3 Lamp F17T8, Prismatic Acrylic Lens