



# 60 Series Exits

## ER60MLD3RB

Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Red Letters, Black Housing and Black Stencil, Emergency Ni-Cad Battery, Self Diagnostics

The 60 Line Max is designed to meet the demands of todays most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

### Product data

<b>General Information</b>		<b>Local order code</b>	7092128
<b>Lamp Source Code</b>	LED	<b>Numerator - Quantity Per Pack</b>	1
<b>Mounting</b>	Wall Suspended	<b>Numerator - Packs per outer box</b>	1
<b>Operating and Electrical</b>		<b>Material Nr. (12NC)</b>	912400372810
<b>Voltages</b>	120/277 V	<b>Net Weight (Piece)</b>	0.001 kg
<b>Luminaire Input Watts</b>	4	<b>Commercial Code</b>	ER60MLD3RB
<b>Product Data</b>		<b>Catalog Number Description</b>	Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Red Letters, Black Housing and Black Stencil, Emergency Ni-Cad Battery, Self Diagnostics
<b>Order product name</b>	ER60MLD3RB	<b>Quick Ship</b>	Service Smart (2 Days) USA
<b>EAN/UPC - Product</b>	781370921286		
<b>Order code</b>	912400372810		