



60 Series Exits

ER60MLD3RGA

Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Red Letters, Gray Housing and Brushed Aluminum Stencil, Emergency Ni-Cad Battery, Self Diagnostics

The 60 Line Max is designed to meet the demands of todays most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

Product data

General Information		Local order code	
Lamp Source Code	LED	Numerator - Quantity Per Pack	1
Mounting	Wall Suspended	Numerator - Packs per outer box	1
Operating and Electrical		Material Nr. (12NC)	912400372811
Voltages	120/277 V	Net Weight (Piece)	0.100 kg
Luminaire Input Watts	4	Commercial Code	ER60MLD3RGA
Product Data		Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Red Letters, Gray Housing and Brushed Aluminum Stencil, Emergency Ni-Cad Battery, Self Diagnostics
Order product name	ER60MLD3RGA	Quick Ship	-
EAN/UPC - Product	781370921293		
Order code	912400372811		