



60 Series Exits

ER60MLD3RW

Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Red Letters, White Housing and White Stencil, Emergency Ni-Cad Battery, Self Diagnostics

The 60 Line Max is designed to meet the demands of todays most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

Product data

General Information		Local order code	7092130
Lamp Source Code	LED	Numerator - Quantity Per Pack	1
Mounting	Wall Suspended	Numerator - Packs per outer box	1
Operating and Electrical		Material Nr. (12NC)	912400372812
Voltages	120/277 V	Net Weight (Piece)	0.001 kg
Luminaire Input Watts	4	Commercial Code	ER60MLD3RW
Product Data		Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Red Letters, White Housing and White Stencil, Emergency Ni-Cad Battery, Self Diagnostics
Order product name	ER60MLD3RW	Quick Ship	Service Smart (2 Days) USA
EAN/UPC - Product	781370921309		
Order code	912400372812		