



# FBF High Bay

## 4', 4 Lamp F32T8, Miro 4 Reflector

4', 4 Lamp F32T8, Miro 4 Reflector

The FBF Fluorescent High Bay is a flexible luminaire designed to meet the needs of today's industrial environment. This luminaire is available with T5HO or T8 lamps. The 95% reflective specular aluminum reflectors and solid body design result in a sturdy and efficient luminaire. A variety of mounting methods and accessories allow the luminaire to be used in many different types of applications.

### Product data

General Information	
Lamp Envelope Code	T-8
Lamp Source Code	Fluorescent
Lamp Watts	32
Number of Lamps	4
Photometric Distribution Type	Direct
Mounting	Suspended
Operating and Electrical	
Voltages	120/208/240/277/347 V
Mechanical and Housing	
Shape	Rectangular

Product Data	
Order product name	FBF432-UNV
EAN/UPC - Product	781370966836
Order code	FBF432-UNV-1/4-EBH
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400373030
Net Weight (Piece)	7.200 kg
Catalog Number	FBF432-UNV-1/4-EBH
Catalog Number Description	4', 4 Lamp F32T8, Miro 4 Reflector