



DuaLED Surface LED

2x4, 7300 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse

2x4, 7300 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse - 99 lm/W

Surface DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare. Optional SpaceWise automated wireless technology provides integrated occupancy and daylight harvesting for additional control and energy savings with no reduction of life.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Surface
Operating and Electrical	
Voltages	120/277/347 V

Luminaire Input Watts	74
Mechanical and Housing	
Fixture Size	2 ft x 4 ft
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	7300
Efficacy	99 lm/W

DuaLED Surface LED

Product Data

Order product name	2SDL73L840-4-D-UNV
EAN/UPC - Product	734340038033
Order code	2SDL73L840-4-D-UNV-DIM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400381687

Net Weight (Piece)	0.100 kg
Catalog Number	2SDL73L840-4-D-UNV-DIM
Catalog Number Description	2x4, 7300 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse

