



# DuaLED Surface LED

**2x4, 5800 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse**

2x4, 5800 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse - 100 lm/W

Surface DuaLED was thoughtfully developed as a sustainable luminaire with a modern appearance and uncomplicated design, also offering exceptional quality and performance, for an outstanding benefit to the customer. DuaLED is a highly efficient, architecturally styled recessed LED luminaire designed with a minimalistic strategy to achieve sustainable objectives. It combines an extremely low profile with clean aesthetics and is powered by highly efficient advanced LED sources, providing the utmost in comfortable efficient lighting. Driver and integral control options ensure optimization for every application. Designed for excellent visual comfort, DuaLED is perfect for a wide variety of general applications like offices, schools, retail, or healthcare. Optional SpaceWise automated wireless technology provides integrated occupancy and daylight harvesting for additional control and energy savings with no reduction of life.

## Product data

General Information		Luminaire Input Watts	
Lamp Source Code	LED	58	
Colour Temperature	4000K	Mechanical and Housing	
CRI	80	Fixture Size	2 ft x 4 ft
Photometric Distribution Type	Direct	Shape	Rectangular
Mounting	Surface	Initial Performance (IEC Compliant)	
Operating and Electrical		Luminaire Lumens	5800
Voltages	120/277/347 V	Efficacy	100 lm/W

## DuaLED Surface LED

### Product Data

Order product name	2SDL58L840-4-D-UNV
EAN/UPC - Product	734340039177
Order code	2SDL58L840-4-D-UNV-DIM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400381715

Net Weight (Piece)	8.100 kg
Catalog Number	2SDL58L840-4-D-UNV-DIM
Catalog Number Description	2x4, 5800 Nominal Delivered Lumens, 4000K, Surface Mount, Diffuse

