



# SofTrace Surface LED

**2x4, Surface, 6300 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Ribbed**

2x4, Surface, 6300 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Ribbed

SofTrace Surface LED brings new meaning to the concept of combining style with performance. Equipped with a fresh streamlined design and innovative technology, SofTrace provides a huge step forward for the lighting industry. The sleek profile design belies the true “horsepower under the hood”. With efficiency levels exceeding 95% and lumens per Watt as great as 87, an architectural product now delivers leading edge performance for the most environmentally conscious user.

## Product data

| General Information                 |               | Product Data                    |  |
|-------------------------------------|---------------|---------------------------------|--|
| Lamp Source Code                    | LED           | Order product name              | 2SST63L840-4-D-UNV   |
| Colour Temperature                  | 4000K         | EAN/UPC - Product               | 782343509449   |
| CRI                                 | 80            | Order code                      | 2SST63L840-4-D-UNV-DIM   |
| Photometric Distribution Type       | Direct        | Numerator - Quantity Per Pack   | 1  |
| Mounting                            | Surface       | Numerator - Packs per outer box | 1  |
| Operating and Electrical            |               | Material Nr. (12NC)             | 912400384270   |
| Voltages                            | 120/277/347 V | Net Weight (Piece)              | 0.400 kg   |
| Luminaire Input Watts               | 65            | Catalog Number                  | 2SST63L840-4-D-UNV-DIM   |
| Mechanical and Housing              |               | Catalog Number Description      | 2x4, Surface, 6300 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse-Ribbed |
| Fixture Size                        | 2 ft x 4 ft   |                                 |  |
| Shape                               | Rectangular   |                                 |  |
| Initial Performance (IEC Compliant) |               |                                 |  |
| Luminaire Lumens                    | 6300          |                                 |  |

## SofTrace Surface LED

