



Rhyno Series NEMA Emergency Unit

Rhyno Series – Polycarbonate NEMA 4X Unit, 12VDC 300W, IP66, Intelli-Charge Diagnostics , Wet Location Listed, High Ambient, -40°C to 40°C, 50W Tungsten Lamps

Rhyno Series – Polycarbonate NEMA 4X Unit, 12VDC 300W, IP66, Intelli-Charge Diagnostics , Wet Location Listed, High Ambient, -40°C to 40°C, 50W Tungsten Lamps

The Rhyno Series features and IP66 rating which is the highest available to resist particulates, oil, water spray down, and othe non-corrosive matter. It is also constructed of impact resistant Lexan and corrosion resistant hardware making it perfect for industrial environments.

Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	50
Number of Lamps	2
Mounting	Wall
Operating and Electrical	
Voltages	120/277 V
Maximum Lamp Watts	50

Product Data	
Order product name	RN230HPE2IC
EAN/UPC - Product	781370004750
Order code	RN230HPE2IC
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400387491
Net Weight (Piece)	0.100 kg
Catalog Number	RN230HPE2IC
Catalog Number Description	Rhyno Series – Polycarbonate NEMA 4X Unit, 12VDC 300W, IP66, Intelli-Charge Diagnostics , Wet Location

Rhyno Series NEMA Emergency Unit

Listed, High Ambient, -40°C to 40°C, 50W Tungsten
Lamps

