



LSW

Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, Two lamp 17 watt T8 24" length luminaire

Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, Two lamp 17 watt T8 24" length luminaire

LSW Lens Wrap Ceiling/Wall Mounted - Specification Grade For ceiling or wall (vertically or horizontally) mounted applications. Only 3 7/8" deep, meets Americans with Disabilities Act (wall mounted). Low brightness .125 thick linear prismatic virgin acrylic refractor. Invisible spring steel latches align refractor to housing. 2 gauge cold rolled steel post painted baked white enamel end caps. For over mirror, over bed, corridor, stairwell and bulletin board applications.

Product data

| | | | |
|---------------------------------|--------------|--|--|
| General Information | | EAN/UPC - Product | 781370073176 |
| Lamp Envelope Code | T-8 | Order code | LS2R217UNVP2 |
| Lamp Watts | 17 | Numerator - Quantity Per Pack | 1 |
| Number of Lamps | 2 | Numerator - Packs per outer box | 1 |
| Mounting | Wall Surface | Material Nr. (12NC) | 912400389310 |
| Operating and Electrical | | Net Weight (Piece) | 0.001 kg |
| Voltages | 277 V | Catalog Number | LS2R217UNVP2 |
| Mechanical and Housing | | Catalog Number Description | Ceiling Or Wall Mounted Fluorescent, 6" Width, 3 7/8" Deep, Two lamp 17 watt T8 24" length luminaire |
| Fixture Size | 24 in | | |
| Product Data | | | |
| Order product name | LS2R217UNV | | |