



# 60 Series LED Exit Sign

**Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Red Letters, Black Housing and Brushed Aluminum Stencil**

Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Red Letters, Black Housing and Brushed Aluminum Stencil

The 60 Line Max is designed to meet the demands of today's most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

## Product data

General information		Product data	
Lamp Source Code	LED	Order product name	60MLA1RBA
Mounting	Wall Suspended	EAN/UPC - Product	781370995331
Number Of Pieces	1	Order code	60MLA1RBA
Buy American Compliant Products	Yes	Numerator - Quantity Per Pack	1
Operating and electrical		Numerator - Packs per outer box	1
Voltages	120/277 V	Material Nr. (12NC)	912400390174
Luminaire Input Watts	4	Net Weight (Piece)	0.001 kg
Conduit Connection	7/8 inch knockout	Catalog Number	60MLA1RBA
Mechanical and housing		Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Single Face, Red Letters, Black Housing and Brushed Aluminum Stencil
Enclosure	Metal and Plastic		