



60 Series Exits

60MLA3GB

Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Green Letters, Black Housing and Black Stencil

The 60 Line Max is designed to meet the demands of todays most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

Product data

General Information	
Lamp Source Code	LED
Mounting	Wall Suspended
Operating and Electrical	
Voltages	120/277 V
Luminaire Input Watts	4
Product Data	
Order product name	60MLA3GB
EAN/UPC - Product	781370995485
Order code	912400390389

Local order code	-
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400390389
Net Weight (Piece)	0.001 kg
Commercial Code	60MLA3GB
Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Green Letters, Black Housing and Black Stencil
Quick Ship	-