



60 Series Exits

60MLA3GGA

Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Green Letters, Gray Housing and Brushed Aluminum Stencil

The 60 Line Max is designed to meet the demands of todays most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

Product data

General Information		Local order code	
Lamp Source Code	LED	Numerator - Quantity Per Pack	1
Mounting	Wall Suspended	Numerator - Packs per outer box	1
Operating and Electrical		Material Nr. (12NC)	912400390397
Voltages	120/277 V	Net Weight (Piece)	0.001 kg
Luminaire Input Watts	4	Commercial Code	60MLA3GGA
Product Data		Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Green Letters, Gray Housing and Brushed Aluminum Stencil
Order product name	60MLA3GGA	Quick Ship	-
EAN/UPC - Product	781370995515		
Order code	912400390397		