



# 60 Series LED Exit Sign

**Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Red Letters, White Housing and Brushed Aluminum Stencil**

Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Red Letters, White Housing and Brushed Aluminum Stencil

The 60 Line Max is designed to meet the demands of today's most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

## Product data

General information		Product data	
Lamp Source Code	LED	Order product name	60MLA3RWA
Mounting	Wall Suspended	EAN/UPC - Product	781370995447
Number Of Pieces	1	Order code	60MLA3RWA
Buy American Compliant Products	Yes	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
Operating and electrical		Material Nr. (12NC)	912400390420
Voltages	120/277 V	Net Weight (Piece)	0.001 kg
Luminaire Input Watts	4	Catalog Number	60MLA3RWA
Conduit Connection	7/8 inch knockout	Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Red Letters, White Housing and Brushed Aluminum Stencil
Mechanical and housing			
Enclosure	Metal and Plastic		