



# 60 Series Exits

## 60MLA3RGA

Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Red Letters, Gray Housing and Brushed Aluminum Stencil

The 60 Line Max is designed to meet the demands of todays most extreme environments. An attractive housing constructed of durable die cast with a polycarbonate backplate and cover. Built for extreme temperatures and vandalproof applications.

### Product data

<b>General Information</b>		<b>Local order code</b>	
Lamp Source Code	LED	Numerator - Quantity Per Pack	1
Mounting	Wall Suspended	Numerator - Packs per outer box	1
<b>Operating and Electrical</b>		Material Nr. (12NC)	912400390479
Voltages	120/277 V	Net Weight (Piece)	0.001 kg
Luminaire Input Watts	4	Commercial Code	60MLA3RGA
<b>Product Data</b>		Catalog Number Description	Wet Location/Vandal Resistant LED Exit, AC Only, Universal Face, Red Letters, Gray Housing and Brushed Aluminum Stencil
Order product name	60MLA3RGA	Quick Ship	-
EAN/UPC - Product	781370995461		
Order code	912400390479		